



Part Number : [936010053](#)

Product Description : GWconnect Turned Crimp Contact for 10A Inserts and Modules, Male, Silver (Ag) Plated Copper Alloy, 0.50mm² (20 AWG), 100 per Bag

Series Number : 93601

Status : Active

Product Category : Heavy-Duty Contacts

Engineering Number : 7100.4212.0



Documents & Resources

Drawings

[Drawing 936010053_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	Heavy-Duty Contacts
Series	93601
Description	GWconnect Turned Crimp Contact for 10A Inserts and Modules, Male, Silver (Ag) Plated Copper Alloy, 0.50mm ² (20 AWG), 100 per Bag
Contact Type	Turned Crimp
Product Family	GWconnect Heavy Duty Connectors (HDC)
Product Name	GWconnect
UPC	887191867519

Agency

CSA	256883
UL	E249674

Electrical

Current - Maximum per Contact	10.0A
-------------------------------	-------

Physical

Gender	Male
Material - Contact	Copper Alloy
Material - Plating	Silver
Net Weight	0.700/g
Number of Grooves	0
Packaging Type	Bag
Stripping Length	8.00mm
Wire Size (AWG)	20
Wire Size mm ²	0.50

Mates With / Use With

Mates with Part(s)

Description	Part Number
GWconnect Heavy-Duty Connectors and Accessories	<u>93601</u>

Use with Part(s)

Description	Part Number
Use With	S-D, S-DD, S-K, S-Q, S-QD, and S-M Inserts
