

Product Code: QOE5232BLK

Description: 3 Pole 2 Way 16A IP66 Connection Box



### Dimensions

|                             |      |
|-----------------------------|------|
| Length (mm)                 | 52   |
| Width (mm)                  | 35.5 |
| Height (mm)                 | 26   |
| Minimum Cable Diameter (mm) | 4    |
| Maximum Cable Diameter (mm) | 6.5  |

### General Information

|                                  |             |
|----------------------------------|-------------|
| Colour                           | Black & Red |
| Operating Voltage - Maximum (AC) | 450         |
| Rated Current (A)                | 16          |
| Tightening Torque (Nm)           | 2.5         |
| Ingress Protection               | IP66        |
| Working Temperature (°C)         | 100         |
| Operational Temperature (°C)     | -40 to +120 |
| Warranty (Years)                 | 1           |

### Materials

Body Components: Nylon (PA66)  
Membranes: Rubber

### Additional Information

2 x PG7 inline entries with seals and membranes.  
Supplied with 3 pole connector block with push-in terminals.

### Standards

BS 6220  
BS EN 60670  
BS EN 60529:1992+A2:2013 (Sections 13 & 14)