



40" Full HD LED Digital TV with built-in Satellite Tuner

- 40" Full HD widescreen LED TV
- Built-in Freeview T2 HD and Digital Freeview Channels
- Built-in satellite tuner
- HDMI input for your external devices and consoles
- Can be wall mounted (200mm x 200mm)

	EAN	5060062269857
Specifications	Model No.	C4020DVB
	Chipset	MSD3663
	Sales Market	England
	VESA Size	200 x 200
	Wall Mount Screws	M5 x 8
	Speaker Output	2 x 8W
	Actual Size of Display (Diagonal)	40"

Display	Display Type	LED
	Resolution	1920 x 1080
	Brightness (nit)	200
	Contrast	3500:1
	Display Colours	16.7M
	Refresh Rate	60Hz
	Viewing Angle H/V	178/178

Accessories	Remote	1
	Battery	AAA x 2

Terminals		
	HDMI Input	3
	RCA Component + AUDIO Input	1
	RCA Composite + AUDIO Input	1
	12-PIN VGA + AUDIO Input	1
	RF Input	1
	Optical Digital AUDIO Input	1
	Coaxial Digital AUDIO Input	0
	Analog AUDIO Output	0
	3.5mm Headphone Output	1

Features		
	DVD	No
	DVB-S	Without
	DVB-S2	Without
	DVB-T+C	With
	DVB-T2+C	With
	CI	With
	3D Digital Comb Filter + 3D Noise Reduction	Yes
	Automatic Volume Control	Yes
	Sleep Timer	Yes
	NO Signal Shut Down	Yes
	Adjustable Bass & Treble Controls	Yes
	Adjustable Balance Control	Yes
	Picture Modes	Standard/Dynamic/Soft/User
	Preset Sound Modes	Standard/Music/Movie/User
	OSD Menu Language	English/French/Spanish/Italy/Germany/Portugal
	Aspect Ratio Modes	Wide/Zoom/Cinema/Normal
	PVR Function	Recording standby, time-shift EPG recording reservation

Power		
	Power Supply	AC 100V-240V - 50Hz/60Hz
	Operation Power Consumption	58W
	Max Power Consumption	70W
	KWh/annum	85kWh
	Standby Consumption	<0.5W
	Energy Efficiency Class	A

Dimensions		
	Unit Dimensions w Stand	907.99 x 257.38 x 571.26
	Unit Dimensions w/o Stand	907.99 x 81.41 x 528.23
	Carton Box Dimensions	1015 x 650 x 160
	Weight (kg)	6.8