



22" Full HD LED TV with Built-in DVD Player

- 22" Full HD widescreen LED TV
- Built-in DVD Player
- Built-in Freeview HD and Digital Freeview Channels
- Satellite tuner built-in
- HDMI input for your external devices and consoles
- Can be wall mounted (100mm x 100mm)

	EAN	5060750400487
Specifications	Model No.	C2220FS
	Chipset	MSD3663
	Sales Market	UK
	VESA Size	100 x 100mm
	Wall Mount Screws	M4 x 8
	Speaker Output	2 x 3W
	Actual Size of Display (Diagonal)	21.5"

Display	Display Type	LED
	Resolution	1920 x 1080
	Brightness (nit)	180
	Contrast	4000:1
	Display Colours	16.7M
	Refresh Rate	60Hz
	Viewing Angle H/V	89/89/89/89
	Reponse Time	6.5ms

ATV System	TV System	PAL/SECAM
	Sound System	BG, DK, I, L/NICAM, A2
	TELETEXT	Yes

DTV System	Receiving modulated signal	Digital Reception VHF & UHF band
	Channel Bandwidth	7MHz/8MHz
	Modulation	DVB-T:COFDM 2K/8K, QPSK,16QAM,64QAM
		DVB-C:16QAM,32QAM,64QAM, 128QAM,256QAM
		DVB-T2:Compliant with EN302755V1.3.1, COFDM: 1K to 32k; SupportT2-Lite,code rate:1/3,2/5; QPSK:16QAM,64QAM,256QAM
		Bandwidth:6,7,8Mhz; Guard Interval:1/128--1/4; Code rate:1/2,3/5,2/3,3/4,4/5,5/6, SPP: PP1 to PP8
		DVB-S2:COFDM 2K/8K, QPSK,8PSK
	Video System	MPEG 2 MP@HL, MPEG-2, MP@HL, H.264
Sound System	Sound System	MPEG-1, MPEG-2(LayerI/II),DD/DD+
	Basic Function	EPG,Subtitle,LCN, TELETXT (Europe), MHEG-5(UK)

Accessories	Remote	1
	Battery	AAA x 2

Terminals	HDMI Input	x1
	MINI Component	x1
	Composite + AUDIO Input	x1
	Optical Digital AUDIO output	x1
	3.5mm Headphone Output	x1
	15-PIN VGA + AUDIO Input	x1
	DVB-S2	x1
	RF Input	x1
	CI	x1
	USB	x1

Features	DVD	Yes
	3D Digital Comb Filter + 3D Noise Reduction	Yes
	Automatic Volume Control	Yes
	Sleep Timer	Yes
	NO Signal Shut Down	Yes
	Adjustable Bass & Treble Controls	Yes
	Adjustable Balance Control	Yes
	Picture Modes	Standard/Dynamic/Personal/Mild
	Preset Sound Modes	Standard/Music/Movie/Personal
	OSD Menu Language	English/French/Spanish/Italy/Germany/Portugal
	Time-shift	Yes
	PVR	Yes
	HDMI Support	480i, 480p, 576i, 576p, 720p, 1080i, 1080p

Power	Power Supply	AC 100V-240V - 50Hz/60Hz
	Operation Power Consumption	21W
	Max Power Consumption	36W
	KWh/annum	31kWh
	Standby Consumption	<1W
	Energy Efficiency Class	F

Dimension	Unit Dimensions w Stand (mm)	504 x 160 x 342
	Unit Dimensions w/o Stand (mm)	504 x 83 x 306
	Weight (kg)	2.55