

# Hermetically Sealed Wire Thermocouple with Bare Tails or Miniature Plug Termination –

Type K, – 1m, 2m, 5m - ANSI



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockists of Thermocouple Cables. The Company has been trading since 1971 and is ISO 9001 accredited.

Labfacility have supplied Farnell for over 30 years, and an extensive range of our products are available to buy online, from stock, direct from Farnell.

# **Datasheet**



An IP67 wire thermocouple that is hermetically sealed for use in corrosive or wet environments.

This versatile multi-purpose sensor has been specifically designed for use in and to protect against corrosion in harsh or wet environments. It has a quick response time and can be easily cleaned. The impermeable PFA insulated flexible wire thermocouple provides exceptional resistance to oils, fluids, gases, and chemicals and is electrically isolated.

The thermocouple tip contains the beaded sensing connection, which is weld-sealed to give a continuous PFA coating along the entire length and provide an atmosphere that is airtight and moisture-proof.

# **Specifications**

	An IP67 wire thermocouple that is hermetically sealed for use in		
General Description	corrosive or wet environments		
Sensor Type	Hermetically sealed		
Thermocouple Type	K		
Cable Length	1m, 2m, 5m		
Cable Type	PFA Flat Pair insulation		
Core / Strands	7/0.2mm (24AWG)		
Termination Type	Bare Tails		
Max. Temperature	+260°C		
Min. Temperature	-75°C		
Tolerance	Class 1		
IP Rating	IP67		
RoHS Compliant	Yes		
Standards Met	ANSI		
Important Information	Pressure tested at 40 PSI as standard		





TC-63 Nov-23

# **Datasheet**



# **Typical Applications**

- Pharmaceutical, Autoclaves and Sterilisation
- Food & Catering
- Environmental
- R & D, temperature mapping and data acquisition

# **Ordering Information**

Туре	Cable Length	Termination	Manufacturers Code	Farnell Order Code
K	1m	Bare Tails	ZX-K-1-C7-T-A	4203758
K	2m	Bare Tails	ZX-K-2-C7-T-A	4203759
K	5m	Bare Tails	ZX-K-5-C7-T-A	4203760
K	1m	Miniature Plug	ZX-K-1-C7-MP-A	4203761
K	2m	Miniature Plug	ZX-K-2-C7-MP-A	4203762
K	5m	Miniature Plug	ZX-K-5-C7-MP-A	4203763

TC-63 Nov-23



### Thermocouple & PRT Cable

Thermocouple cables are available in IEC or ANSI colour codes. Insulation types include PFA, PTFE, PVC &

Fibreglass. Available spool lengths include 10, 25, 50, 100 and 200m.

### Best Sellers 📥



**ANSI PTFE** Insulated Twin Twisted Farnell 2443696 Newark 73AC8304

**ANSI PFA Insulated** Twin Twisted Farnell 2443711 Newark 73AC8297

### **Fabricated and Specialist** Thermocouples

Styles include; Magnet, Washer, Nozzle, Leaf, Bayonet & Bolt thermocouple, Various lengths and calibration types available.

### Best Sellers



Washer Thermocouple Farnell 8597952 Newark 38K1555

**Bayonet** Thermocouple Farnell 2785115 Newark 37AC0993

Magnet Thermocouple Farnell 2081298 Newark 88T2877

#### **Exposed Junction** Thermocouples

Including exposed junctions with fitted or moulded miniature plug and insulated leads, ideal for test and development applications.

1, 2, 3, 5 & 10m lengths available in IEC or ANSI colours.

### Best Sellers



**IEC Type T Exposed** Junction Farnell 7076186 Newark 68C2613

IEC Type K Exposed Junction Farnell 4100748 Newark 15J1022



#### **Thermocouple Connectors**

Range of miniature or standard thermocouple connectors. Available in thermocouple types K, J, T, E, N, RS, B, and copper. IEC, ANSI & JIS colour codes available.

# Best Sellers



**IEC Thermocouple PCB Socket** Farnell 2347056 Newark 06X5514



**IEC Thermocouple** Plug

Farnell 7086362 Newark 67C1559



ANSI Thermocouple Socket

> Farnell 2347121 Newark 06X4819



#### **RTD Detectors**

Wire-wound type provides greater accuracy and stability but are vulnerable to shock.

Flat film type are resistant to shock and have quicker thermal response times.

Various lengths and diameters available, in class A, B and 1/10th Din.

## **Best Sellers**



Film Detector Farnell 8598550 Newark 38K0883

PT100 Wire **Wound Detector** 

Farnell 2770776 Newark 25AC2608

PT100 Class A Thin Film Detector

Farnell 8598525 **Newark 38K0885** 



## Mineral Insulated Thermocouples

Available in various calibration types with a variety of terminations

These include; Thermocouple plugs, Terminal heads and Thermocouple cable.





**ANSI Thermocouple** Farnell 2420317 **Newark 53X3217** 

IEC Thermocouple with Mini Plug

Farnell 4248338 **Newark 19J1166** 

**IEC Melt Bolt** Thermocouple Farnell 2816490 Newark 44AC8638



### **Best Sellers**



Pt100 Heavy Duty Sensor Probe Farnell 8598096 Newark 38K0974



Pt100 Sensor in Stainless Steel Tube with Teflon Lead Farnell 2420300 Newark 53X3459

Pt100 Outdoor/ Cold Store Temperature Sensor Farnell 2816462 Newark 44AC8648

#### L60 Fine Wire Thermocouple Welder

The Thermocouple Welder is a compact, simple-to-use instrument designed for thermocouple and fine wire welding. Supplied with foot switch, spare electrodes, pliers & safety glasses, impact clip and pen plate.

# Best Sellers







L60+ Thermocouple & Fine Wire Welder and accessories Farnell 2897470 Newark 62AC8741

Resistance Thermometer Detectors (RTD) / Platinum Resistance Thermometers (PRT)

To suit a wide range of applications and styles, available in class A or B.



TC-63 Nov-23