



## 32" HD LED Digital TV with built-in Satellite Tuner

- 32" HD Ready widescreen LED TV
- Built-in Freeview T2 HD and Digital Freeview Channels
- Built-in satellite tuner
- HDMI input for your external devices and consoles
- Can be wall mounted (100mm x 100mm)

|                | EAN                               | 5060062269819     |
|----------------|-----------------------------------|-------------------|
| Specifications | Model No.                         | C3220DVB          |
|                | Chipset                           | MSD3663           |
|                | Sales Market                      | England           |
|                | VESA Size                         | 100 x 100         |
|                | Wall Mount Screws                 | M5 x 8            |
|                | Speaker Output                    | 2 x 8W            |
|                | Actual Size of Display (Diagonal) | 31.5"             |
| Display        | Display Type                      | LED               |
|                | Resolution                        | 1366 x 768 (16:9) |
|                | Brightness (nit)                  | 200               |
|                | Contrast                          | 1200:1            |
|                | Display Colours                   | 16.7M             |
|                | Refresh Rate                      | 60Hz              |
|                | Viewing Angle H/V                 | 178/178           |
| Accessories    | Remote                            | 1                 |
|                | Battery                           | AAA x 2           |



|                  |                   |                                                                            |
|------------------|-------------------|----------------------------------------------------------------------------|
| <b>Terminals</b> | RF Antenna        | x2 (1 x DVB-T/T2 & 1 x DVB-S/S2)                                           |
|                  | HDMI              | x3                                                                         |
|                  | CVBS              | YES x 1(3.5 φ Mini Jack)                                                   |
|                  | Audio In          | PC audio x 1(3.5 φ Mini Jack), CVBS Audio x1(Mini Jack,Shared with Ypbpr)" |
|                  | Scart             | x1                                                                         |
|                  | YPbPr             | YES x 1(3.5 φ Mini Jack)                                                   |
|                  | Digital Audio out | x1                                                                         |
|                  | Earphone Out      | x1                                                                         |
|                  | USB on TV         | x1                                                                         |
|                  | CI                | x1                                                                         |

|                 |                                             |                                               |
|-----------------|---------------------------------------------|-----------------------------------------------|
| <b>Features</b> | DVD                                         | No                                            |
|                 | DVB-S                                       | With                                          |
|                 | DVB-S2                                      | With                                          |
|                 | DVB-T+C                                     | With                                          |
|                 | DVB-T2+C                                    | With                                          |
|                 | CI                                          | With                                          |
|                 | 3D Digital Comb Filter + 3D Noise Reduction | Yes                                           |
|                 | Automatic Volume Control                    | Yes                                           |
|                 | Sleep Timer                                 | Yes                                           |
|                 | NO Signal Shut Down                         | Yes                                           |
|                 | Adjustable Bass & Treble Controls           | Yes                                           |
|                 | Adjustable Balance Control                  | Yes                                           |
|                 | Picture Modes                               | Standard/Dynamic/Soft/User                    |
|                 | Preset Sound Modes                          | Standard/Music/Movie/User                     |
|                 | OSD Menu Language                           | English/French/Spanish/Italy/Germany/Portugal |
|                 | Aspect Ratio Modes                          | Wide/Zoom/Cinema/Normal                       |
|                 | PVR Function                                | Recording standby, time-shift                 |
|                 |                                             | EPG recording reservation                     |

|              |                             |                          |
|--------------|-----------------------------|--------------------------|
| <b>Power</b> | Power Supply                | AC 100V-240V - 50Hz/60Hz |
|              | Operation Power Consumption | 34W                      |
|              | Max Power Consumption       | 60W                      |
|              | KWh/annum                   | 50kWh                    |
|              | Standby Consumption         | <0.5W                    |
|              | Energy Efficiency Class     | E                        |

|                   |                           |                          |
|-------------------|---------------------------|--------------------------|
| <b>Dimensions</b> | Unit Dimensions w Stand   | 730.26 x 468.88 x 195.29 |
|                   | Unit Dimensions w/o Stand | 730.26 x 430.76 x 94     |
|                   | Carton Box Dimensions     |                          |
|                   | Weight (Kg)               | 4.3                      |