

3680 Wyse Road Dayton Ohio 45414-5802 Phone: 937-918-2200 Fax: 937-918-2206

Audio@ProjectsUnlimited.com

Part Number: AT-1620-TWT-12V-R



Features

Mounting: Thru Hole Tone: Continuous Frequency: 2048 +/- 500 Hz Lead Free Component

Electrical Specifications

Operating Voltage 9 +/- 15 Vp-p
Rated Current (Max.) 40 mA
Rated Voltage 12 Vp-p
Resonant Frequency 2048 +/- 500 Hz


Sound Pressure Level @ 10 cm (Min.) 85 dBA

Case: Noryl Weight: 5 g

Pin Material: SnBi plated copper Environmentally friendly, lead free


Mechanical

Dimensions are in millimeters, tolerance is \pm 0.5 unless otherwise specified.



Performance

Typical SPL vs. Frequency



For application notes and detail drawing specifications, please consult www.projectsunlimited.com.

Specifications subject to change without notice.

© 2005, Projects Unlimited Inc., All Rights Reserved.