

INTRODUCTION

This gold-plated IPEX MHF1 to SMA female connector has passed 48 hours salt spray test, which is durable and not easy to rust.



It adopts RG1.13 wire material and high-density shielding layer, soft and firm, fold-resistant and durable, with fast and stable data transmission.



These IPEX MHF1 to SMA Female Cables can be widely used in WiFi, GPS, 4G, 5G, and other modules.

SPECIFICATION

- Applicable Frequency Band: 0-6G
- Bandwidth: 100Mhz
- Standing Wave Ratio: ≤ 1.5
- Interface: IPEX MHF1 to SMA

- Impedance: 50Ω
- Line Length: 10cm
- Wire: RG1.13

SHIPPING LIST

- IPEX MHF1 to SMA Female Cable x2