

LOWERS YOUR BARRIER TO ENTRY FOR IIOT.

SNAP SIGNAL LOWERS YOUR



DX80N9Q45UPSD-PS150

▶ PRODUCTS FOR INDUSTRIAL AUTOMATION



Wireless Q45 900 MHz Node 1 W

Pre-Wired Female M12 QD for BWA-PRESSURE-
SENSOR-150 (Sensor/Cable Assembly Included)

D-Cell Battery Included

Part Number: 815342

CERTIFICATIONS



SPECIFICATIONS

Power	Battery
IP Rating	IP67
Banner Cloud ID	Yes
Housing Style	Integrated Battery
Device Type	Sensor and Node
Input Output	Analog
Analog Inputs	Yes
Input Details	0-5 VDC
Power Supply	D Cell Lithium Battery
Environmental Rating (NEMA)	NEMA 6P
Max Temp Operating Conditions (°C)	70
Min Temp Operating Conditions (°C)	-40

Ships With Battery	Yes
Point-to-Multipoint Topology	Yes
Point-to-Point Topology	Yes
Star Topology	Yes
Tree Topology	No
Feature: Hazardous Area	No
Application: Temperature Input	Yes
Pressure Sensor Input	Yes
Pressure Sensor Range (PSI)	0-150
Wireless	Yes
Wireless Radio Frequency	900 MHz



Banner Engineering Corp. | 9714 Tenth Avenue North | Minneapolis, MN 55441 |
United States of America

