

MobileGlue 5011

including rechargeable 2,0 Ah battery and charger
 EAN 4007841 085384
 Article number 085384



Serie 5

ø 11 mm


Klebesticks

20 g/min

Fördermenge



2 Stufen 130°C /
200°C



austauschbare Düse



punktgenaues
Arbeiten



Quick Start 2min



Akku-Laufzeit



Eco-Mode
(automatisches
Abschalten)



no memory effect

Function description

Professional, cordless and powerful bonding for up to 90 minutes. The MG 5011 with 18V CAS battery system has two temperature settings of 130 °C/200 °C and an extra-high flow rate of 20 g/min.

Technical specifications

Temperature	130 – 200 °C
Warm-up time	1,5 min
Delivery rate	20 gr/min
Max. stick diameter	11 mm
Temperature display	LED segment display
Function, hanger	No
Soft grip	Yes
Idle mode	No
Nozzle can be changed	Yes
Stroke adjustment	No
Temperature, adjustable	Yes
Temperature accuracy +/-	5 °C
Heating element	PTC heating element
Voltage range (min)	18 V

Rechargeable battery run time	up to 90 minutes
Rechargeable battery voltage	18 V
Rechargeable battery capacity	2 Ah
Rechargeable battery type	Li-ion
Restart protection	No
Power supply, detail	Rechargeable lithium-ion battery
Suitable for	Sheetings, Glass, Wood, ceramic, Leather, Metal, Paper, Card / cardboard boxes, Tarpaulins, Plexiglas®, Polystyrene, Textiles
Melt temperature	130 – 200 °C
Dimensions (L x W x H)	256 x 78 x 188 mm
Version	including rechargeable 2,0 Ah battery and charger
PU1, net weight	0,375 kg
Manufacturer's Warranty	1 year
PU1, EAN	4007841085384
Scope of delivery	incl. 18V 2,0 Ah CAS battery, CAS charger & 3 glue sticks

Cordless hot-melt glue applicator - Professional Line

MobileGlue 5011

including rechargeable 2,0 Ah battery and charger

EAN 4007841 085384

Article number 085384



Accessories

EAN 4007841 050092	General-purpose glue sticks Ø 11 mm
EAN 4007841 052416	Acrylate glue sticks Ø 11 mm
EAN 4007841 052430	Fast glue sticks Ø 11 mm
EAN 4007841 052423	Flex glue sticks Ø 11 mm
EAN 4007841 052409	Low Melt glue sticks Ø 11 mm