



VT 40W LED SOLAR FLOODLIGHT 6400K 5000 mAh BATTERY 3M CABLE SMART IR REMOTE FAST CHARGE



FEATURES

- Solar Powered Floodlight - Zero electricity cost
- Designed with Remote control, Auto and timer function
- Flexible installation, designed with solar panel with 3m wire length
- Solar panel Dimension:174x260mm
- Perfectly built for outdoor with Ingress protection of IP65
- Suitable for Pathways, Garden, Patio and similar outdoor environment

TECHNICAL INFORMATION

| | |
|------------------------|-----------------------|
| Output Voltage: | DC:6V |
| Solar Panel: | 6W |
| Model: | VT-40W |
| Working Time: | 12 Hours |
| Battery Type: | 3.2V, 5000mAh Battery |
| Beam Angle: | 120° |
| Color Temperature: | 6400K |
| Lumens: | 400 |
| Unit Color: | Black |
| Color for Web: | White |
| Body Type: | Aluminium |
| Dimension: | 190x55x170mm |
| Operation Temperature: | -20°C to +60°C |
| LED Chip Type: | SMD |
| Wire Length: | 3m |
| IK Rating: | IK06 |
| Charging Time: | 4-6 Hours |
| IP Rating: | IP65 |

IP65
STANDARD

02
YEAR
WARRANTY

LISTING DETAILS

| | |
|-----------------|---------------|
| SKU: | 7821 |
| Model: | VT-40W |
| EAN: | 3800170200470 |
| Commodity Code: | 94054110 |

PACKAGING

| | |
|---------------------|--------------|
| Gross Weight (Kgs): | 1.42 |
| Unit CBM: | 0.004276 |
| Dimension: | 190x55x170mm |

MASTER BOX PACKAGING

| | |
|------------------|-----|
| Box Qty: | 10 |
| Qty Per Pallet: | |
| Length (Box) mm: | 182 |
| Width (Box) mm: | 76 |
| Height (Box) mm: | 270 |