



**VT 40W LED SOLAR FLOODLIGHT 4000K 5000  
mAh BATTERY 3M CABLE SMART IR REMOTE  
FAST CHARGE**



**FEATURES**

- Solar Powered Floodlight - Zero electricity cost
- Designed with Remote control, Auto and timer function
- Flexible installation, designed with solar panel with 3m wire length
- Solar panel Dimension:174x260mm
- Perfectly built for outdoor with Ingress protection of IP65
- Suitable for Pathways, Garden, Patio and similar outdoor environment

**TECHNICAL INFORMATION**

Output Voltage:	DC:6V
Solar Panel:	6W
Model:	VT-40W
Working Time:	12 Hours
Battery Type:	3.2V, 5000mAh Battery
Beam Angle:	120°
Color Temperature:	4000K
Lumens:	400
Unit Color:	Black
Color for Web:	Day White
Body Type:	Aluminium
Dimension:	190x55x170mm
Operation Temperature:	-20°C to +60°C
LED Chip Type:	SMD
Wire Length:	3m
IK Rating:	IK06
Charging Time:	4-6 Hours
IP Rating:	IP65

**IP65**  
STANDARD

**02**  
YEAR  
WARRANTY

**LISTING DETAILS**

SKU:	7822
Model:	VT-40W
EAN:	3800170200487
Commodity Code:	94054110

**PACKAGING**

Gross Weight (Kgs):	1.42
Unit CBM:	0.00428
Dimension:	190x55x170mm

**MASTER BOX PACKAGING**

Box Qty:	10
Qty Per Pallet:	
Length (Box) mm:	182
Width (Box) mm:	76
Height (Box) mm:	270