



VT 80W LED SOLAR FLOODLIGHT 4000K 6000mAh BATTERY 3M CABLE SMART IR REMOTE FAST CHARGE



FEATURES

- Solar Powered Floodlight - Zero electricity cost
- Designed with Remote control, Auto and timer function
- Flexible installation, designed with solar panel with 3m wire length
- Solar panel Dimension:174x340mm
- Perfectly built for outdoor with Ingress protection of IP65
- Suitable for Pathways, Garden, Patio and similar outdoor environment

TECHNICAL INFORMATION

Output Voltage:	DC:6V
Solar Panel:	10W
Model:	VT-80W
Working Time:	12 Hours
Battery Type:	3.2V, 6000mAh Battery
Beam Angle:	120°
Color Temperature:	4000K
Lumens:	800
Unit Color:	Black
Color for Web:	Day White
Body Type:	Aluminium
Dimension:	190x55x170mm
Operation Temperature:	-20°C to +60°C
LED Chip Type:	SMD
Wire Length:	3m
IK Rating:	IK06
Charging Time:	4-6 Hours
IP Rating:	IP65

IP65
STANDARD

02
YEAR
WARRANTY

LISTING DETAILS

SKU:	7824
Model:	VT-80W
EAN:	3800170200500
Commodity Code:	94054110

PACKAGING

Gross Weight (Kgs):	1.54
Unit CBM:	0.005476
Dimension:	190x55x170mm

MASTER BOX PACKAGING

Box Qty:	10
Qty Per Pallet:	
Length (Box) mm:	182
Width (Box) mm:	76
Height (Box) mm:	350