



VT 120W LED SOLAR FLOODLIGHT 6400K 12000mAh BATTERY 3M CABLE SMART IR REMOTE FAST CHARGE



FEATURES

- Solar Powered Floodlight - Zero electricity cost
- Designed with Remote control, Auto and timer function
- Flexible installation, designed with solar panel with 3m wire length
- Solar panel Dimension: 235x350mm
- Perfectly built for outdoor with Ingress protection of IP65
- Suitable for Pathways, Garden, Patio and similar outdoor environment

TECHNICAL INFORMATION

Output Voltage:	DC:6V
Solar Panel:	15W
Model:	VT-120W
Working Time:	12 Hours
Battery Type:	3.2V, 12000mAh Battery
Beam Angle:	120°
Color Temperature:	6400K
Lumens:	1200
Unit Color:	Black
Color for Web:	White
Body Type:	Aluminium
Dimension:	235x55x180mm
Operation Temperature:	-20°C to +60°C
LED Chip Type:	SMD
Wire Length:	3m
IK Rating:	IK06
Charging Time:	4-6 Hours
IP Rating:	IP65

IP65
STANDARD

02
YEAR
WARRANTY

LISTING DETAILS

SKU:	7825
Model:	VT-120W
EAN:	3800170200517
Commodity Code:	94054110

PACKAGING

Gross Weight (Kgs):	2.116666
Unit CBM:	0.007585
Dimension:	235x55x180mm

MASTER BOX PACKAGING

Box Qty:	6
Qty Per Pallet:	
Length (Box) mm:	245
Width (Box) mm:	76
Height (Box) mm:	360