



# VT 120W LED SOLAR FLOODLIGHT 4000K 12000mAh BATTERY 3M CABLE SMART IR REMOTE FAST CHARGE



## FEATURES

- Solar Powered Floodlight - Zero electricity cost
- Designed with Remote control, Auto and timer function
- Flexible installation, designed with solar panel with 3m wire length
- Solar panel Dimension: 235x350mm
- Perfectly built for outdoor with Ingress protection of IP65
- Suitable for Pathways, Garden, Patio and similar outdoor environment

## TECHNICAL INFORMATION

|                        |                        |
|------------------------|------------------------|
| Output Voltage:        | DC:6V                  |
| Solar Panel:           | 15W                    |
| Model:                 | VT-120W                |
| Working Time:          | 12 Hours               |
| Battery Type:          | 3.2V, 12000mAh Battery |
| Beam Angle:            | 120°                   |
| Color Temperature:     | 4000K                  |
| Lumens:                | 1200                   |
| Unit Color:            | Black                  |
| Color for Web:         | Day White              |
| Body Type:             | Aluminium              |
| Dimension:             | 235x55x180mm           |
| Operation Temperature: | -20°C to +60°C         |
| LED Chip Type:         | SMD                    |
| Wire Length:           | 3m                     |
| IK Rating:             | IK06                   |
| Charging Time:         | 4-6 Hours              |
| IP Rating:             | IP65                   |

**IP65**  
STANDARD

**02**  
YEAR  
WARRANTY

## LISTING DETAILS

|                 |               |
|-----------------|---------------|
| SKU:            | 7826          |
| Model:          | VT-120W       |
| EAN:            | 3800170200524 |
| Commodity Code: | 94054110      |

## PACKAGING

|                     |              |
|---------------------|--------------|
| Gross Weight (Kgs): | 2.116666     |
| Unit CBM:           | 0.007566     |
| Dimension:          | 235x55x180mm |

## MASTER BOX PACKAGING

|                  |     |
|------------------|-----|
| Box Qty:         | 6   |
| Qty Per Pallet:  |     |
| Length (Box) mm: | 245 |
| Width (Box) mm:  | 76  |
| Height (Box) mm: | 360 |