



VT-239 2.9W R39 PLASTIC BULB SAMSUNG CHIP 3000K



FEATURES

- Modern LED SMD-Samsung Chip technology for better reliability and durability
- Replaces 25 watts old halogen lamp
- Lasts hours, longer life span than Standard halogen lamps
- Designed for E14 standard holder
- Suitable for residential lighting, commercial lighting, decorative, living rooms, lounges etc.

TECHNICAL INFORMATION

Model:	VT-239-N
On/Off Cycles:	>20000
CRI:	>80
Beam Angle:	120°
Color Temperature:	3000K
Watts:	2.9
Lumens:	250
Input Power:	AC:220-240V, 50Hz
Equivalence Watts:	25
Unit Color:	White
Color for Web:	Warm White
Body Type:	Plastic
Dimension:	39x67mm
Operation Temperature:	-20°C to +45°C
Base:	E14
Shape:	R39
LED Chip Type:	SMD-Samsung Chip
Energy Rating Label:	F (2021)
Energy Saving:	85 Energy
Samsung:	Yes
Long Life:	20,000 Hours
IP Rating:	IP20

IP20
STANDARD

05
YEAR
WARRANTY



LISTING DETAILS

SKU:	21210
Model:	VT-239-N
EAN:	3800170203228
Commodity Code:	85395200

PACKAGING

Gross Weight (Kgs):	0.02
Unit CBM:	0.000144
Dimension:	39x67mm

MASTER BOX PACKAGING

Box Qty:	200
Qty Per Pallet:	
Length (Box) mm:	39
Width (Box) mm:	39
Height (Box) mm:	75