



VT-1819 3.7W P45 LED PLASTIC BULB 6500K E14



FEATURES

- Modern LED SMD technology for better reliability and durability
- Replaces 25 watts old halogen lamp
- Lasts hours, longer life span than Standard halogen lamps
- Designed for E14 standard holder
- Suitable for residential lighting, commercial lighting, decorative, living rooms, lounges etc.

TECHNICAL INFORMATION

Dimmable:	No
Model:	VT-1819-N
Instant Start:	0-100% in <1s
On/Off Cycles:	>20000
Inner Box Qty:	5
CRI:	>80
Beam Angle:	180°
Color Temperature:	6500K
Watts:	3.7
Lumens:	320
Input Power:	AC:220-240V, 50Hz
Equivalence Watts:	25
Unit Color:	White
Color for Web:	White
Body Type:	Thermoplastic
Dimension:	45x80mm
Operation Temperature:	-20°C to +45°C
Base:	E14
Shape:	P45
PF:	>0.4
LED Chip Type:	SMD
Energy Rating Label:	F (2021)
Energy Saving:	80 Energy
Long Life:	25,000 Hours
IP Rating:	IP20

IP20
STANDARD

02
YEAR
WARRANTY

LISTING DETAILS

SKU:	214124
Model:	VT-1819-N
EAN:	3800157665407
Commodity Code:	85395200

PACKAGING

Gross Weight (Kgs):	0.02
Unit CBM:	0.000225
Dimension:	45x80mm

MASTER BOX PACKAGING

Box Qty:	5
Qty Per Pallet:	6800
Length (Box) mm:	46
Width (Box) mm:	46
Height (Box) mm:	82