



VT-247 6W GU10 RIPPLE PLASTIC SPOTLIGHT SAMSUNG CHIP 3000K 110'D



FEATURES

- Stable SMD-Samsung Chip technology for better reliability
- Lasts hours, longer life span than Standard halogen spotlights
- Replaces watts old halogen lamp
- Easy to install, designed with GU10 base
- Applications - Hotels, Bars, Commercial and Residential Lighting and Exhibition Stands etc

TECHNICAL INFORMATION

Model:	VT-247
On/Off Cycles:	>20000
CRI:	>80
Beam Angle:	110°
Color Temperature:	3000K
Watts:	6
Lumens:	445
Input Power:	AC:220-240V, 50Hz
Equivalence Watts:	60
Unit Color:	White
Color for Web:	Warm White
Body Type:	Plastic
Dimension:	50x55mm
Operation Temperature:	-20°C to +45°C
Base:	GU10
LED Chip Type:	SMD-Samsung Chip
Energy Rating Label:	F (2021)
Energy Saving:	85 Energy
Samsung:	Yes
Long Life:	20,000 Hours
IP Rating:	IP20

IP20
STANDARD

05
YEAR
WARRANTY



LISTING DETAILS

SKU:	21192
Model:	VT-247
EAN:	3800170207363
Commodity Code:	

PACKAGING

Gross Weight (Kgs):	0.03
Unit CBM:	0.000248
Dimension:	50x55mm

MASTER BOX PACKAGING

Box Qty:	200
Qty Per Pallet:	
Length (Box) mm:	50
Width (Box) mm:	50
Height (Box) mm:	80