

SAMSUNG HG43ET670



DISPLAY

Display diagonal 108 cm (42.5")
HD type HD type 4K Ultra HD
Display resolution 3840 x 2160 pixels
Display technology Display technology LED
Native aspect ratio 16:9
Dynamic contrast ratio marketing name Mega Contrast
Display diagonal (metric) Display diagonal (metric) 108 cm

DESIGN

Product colour Product colour Black
VESA mounting Yes
Panel mounting interface Panel mounting interface 200 x 200 mm

PERFORMANCE

High Dynamic Range (HDR) supported Yes
High Dynamic Range (HDR) technology High Dynamic Range 10+ (HDR10 Plus), Hybrid Log-Gamma (HLG)
Tuner type Analog & digital
Digital signal format system ATSC, DVB-C, DVB-S2, DVB-T, DVB-T2
On Screen Display (OSD) Yes
Electronic Programme Guide (EPG) Yes
Auto power off Yes
Sleep timer Yes
Hybrid Broadcast Broadband TV (HbbTV) Yes
ConnectShare (HDD) Yes
ConnectShare (USB) Yes
Teletext function Yes

AUDIO

Number of speakers 2
RMS rated power 20 W
Audio decoders Dolby Digital Plus

HOSPITALITY FEATURES

Hospitality home menu Yes
Hotel channel list Yes
Hospitality Plug and Play Yes
Welcome message Yes
Clock back up supply Yes
My Channel function Yes
USB cloning Yes
Smovie compatibility Yes
Soundbar compatibility Yes
Content management solution Samsung LYNK REACH LYNK REACH version 4.0
Security mode Yes

PORTS & INTERFACES

HDMI ports quantity 3
USB 2.0 ports quantity 2
Digital audio optical out 1
PC Audio in PC Audio in Yes
RJ-12 ports quantity 1
Common interface (CI) Yes
Common interface Plus (CI+) Yes
Common interface Plus (CI+) version 1.4

POWER

Power consumption (typical) 75 W
Power consumption (standby) 0.5 W
Energy consumption (SDR) per 1000 hours 73 kWh
Energy consumption (HDR) per 1000 hours 101 kWh
Energy efficiency class (SDR) G
Energy efficiency class (HDR) G

WEIGHT & DIMENSIONS

With stand (W x H x D) 964 x 611 x 226.5 mm
Without stand (W x H x D) 964 x 559 x 60 mm
Weight 15 kg