

RoHS  
Compliant



## Specifications

Conductor Material : Stranded Tinned Copper  
 Insulation Material : PVC  
 Rated Temperature : 105°C  
 Rated Voltage : 600V  
 Safety Certifications : UL1015  
 Cable Length : Available in 30.5m / 100ft Reels

## Specification Table

Part Number	Construction Strands/ Strand Size (mm)	Conductor Diameter (mm)	Insulation Diameter (mm)	Conductor Resistance 20°C (Ω/kM)	Wire Gauge AWG	Insulation Color
MP011190	41/0.254	1.88	3.5	8.62	14	Black
MP011191	41/0.254	1.88	3.5	8.62	14	Red
MP011192	41/0.254	1.88	3.5	8.62	14	White
MP011193	41/0.254	1.88	3.5	8.62	14	Green
MP011194	41/0.254	1.88	3.5	8.62	14	Green/Yellow
MP011195	65/0.16	1.49	3.1	13.7	16	Black
MP011196	65/0.16	1.49	3.1	13.7	16	Red
MP011197	65/0.16	1.49	3.1	13.7	16	White
MP011198	65/0.16	1.49	3.1	13.7	16	Green/Yellow
MP011199	34/0.18	1.21	2.8	21.86	18	Black
MP011200	34/0.18	1.21	2.8	21.86	18	Red
MP011201	34/0.18	1.21	2.8	21.86	18	White
MP011202	34/0.18	1.21	2.8	21.86	18	Blue
MP011203	34/0.18	1.21	2.8	21.86	18	Green/Yellow
MP011204	17/0.16	0.76	2.3	55	22	Black
MP011205	17/0.16	0.76	2.3	55	22	Red
MP011206	17/0.16	0.76	2.3	55	22	White
MP011207	17/0.16	0.76	2.3	55	22	Yellow
MP011208	17/0.16	0.76	2.3	55	22	Blue
MP011209	11/0.16	0.61	2.2	93.25	24	Black
MP011210	11/0.16	0.61	2.2	93.25	24	Red
MP011211	11/0.16	0.61	2.2	93.25	24	White

## Part Number Table

Description	Insulation Color	Part Number
Hook-up Wire, UL1015, PVC, 100ft (30.5m)	Black	MP011190
	Red	MP011191
	White	MP011192
	Green	MP011193
	Green/Yellow	MP011194
	Black	MP011195
	Red	MP011196
	White	MP011197
	Green/Yellow	MP011198
	Black	MP011199
	Red	MP011200
	White	MP011201
	Blue	MP011202
	Green/Yellow	MP011203
	Black	MP011204
	Red	MP011205
	White	MP011206
	Yellow	MP011207
	Blue	MP011208
	Black	MP011209
Red	MP011210	
White	MP011211	

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.