Part Number : 348403410
Product Description : MX150 Male Connector Assembly, Bulkhead Twist-Lock, Mat-Sealed Compatible, Dual Row, 6 Circuits, Keying Option A, Black
Series Number : 34840
Status : Active
Product Category : Connector Housings



Documents & Resources

Drawings

Drawing_348403410_sd.pdf
Packaging Design Drawing_PK-31301-615-001.pdf

3D Models and Design Files

3D Model_348403410_stp.zip

Specifications

Application Specification_AS-34840-001-001.pdf
Product Specification_PS-34840-0001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Connector Housings
Series	34840
Description	MX150 Male Connector Assembly, Bulkhead Twist-Lock, Mat-Sealed Compatible, Dual Row, 6 Circuits, Keying Option A, Black
Application	Power, Wire-to-Wire
Product Family	MX150 Sealed and Unsealed Connector System
Product Name	MX150
UPC	191128253857

Physical

Circuits (maximum)	6
Color - Resin	Black, Natural
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Modified Polystyrene Alloy
Net Weight	17.390/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
MX150 Mat-Sealed Dual Row Female Connector Assemblies	33472

Use with Part(s)

Description	Part Number
MX150 Male Terminals	33000