



VT-246 4.5W G45 PLASTIC BULB SAMSUNG CHIP
3000K E27



FEATURES

- Modern LED SMD-Samsung Chip technology for better reliability and durability
- Replaces 40 watts old halogen lamp
- Lasts hours, longer life span than Standard halogen lamps
- Designed for E27 standard holder
- Suitable for residential lighting, commercial lighting, decorative, living rooms, lounges etc.

TECHNICAL INFORMATION

Model:	VT-246-N
On/Off Cycles:	>20000
CRI:	>80
Beam Angle:	180°
Color Temperature:	3000K
Watts:	4.5
Lumens:	470
Input Power:	AC:220-240V, 50Hz
Equivalence Watts:	40
Unit Color:	White
Color for Web:	Warm White
Body Type:	Thermoplastic
Dimension:	45x80mm
Base:	E27
Shape:	G45
LED Chip Type:	SMD-Samsung Chip
Energy Rating Label:	F (2021)
Energy Saving:	85 Energy
Samsung:	Yes
Long Life:	20,000 Hours
IP Rating:	IP20

IP20
STANDARD

05
YEAR
WARRANTY



LISTING DETAILS

SKU:	21174
Model:	VT-246-N
EAN:	3800157698573
Commodity Code:	85395200

PACKAGING

Gross Weight (Kgs):	0.03
Unit CBM:	0.000216
Dimension:	45x80mm

MASTER BOX PACKAGING

Box Qty:	200
Qty Per Pallet:	
Length (Box) mm:	46
Width (Box) mm:	46
Height (Box) mm:	82