

DATA SHEET

53112000

SKINTOP[®] MS-M / MSR-M

valid from : 22.05.2006

The SKINTOP[®] MS-M / MSR-M a nickel-plated brass cable gland with metric connecting thread which combines high quality with regard to consistency and reliability, is especially designed for use in manufacturing of machines and equipment, in measuring, controlling as well as in the pharmaceutical industry and for medical equipment.

The gland make-up consists of:

Gland body with lamellar design Cap nut Insert with lamellar design Seal insert Sealing ring nickel-plated brass nickel-plated brass plastic polyamide-based elastomere elastomere

Technical features:

Connecting thread: IP protection: Temperature range: Type: M 12 up to M 63 in acc. to EN 60423 IP 68 - 5 bar, test in acc. to EN 60529, - 25°C up to + 100°C MS-M = standard; MSR-M = standard with reducing seal insert

Approval:



For more information please see our current catalogue. Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.

