



# VT-44010 10W FLOODLIGHT SAMSUNG CHIP 4000K BLACK BODY GREY GLASS



## FEATURES

- High quality LED SMD-Samsung Chip chip and high power driver
- Comparing with traditional halogen floodlights it can save upto 85% Energy
- Constant current Integrated IC driver - Built in driver - no external power supply required
- Built Strong and durable with Aluminium - Corrosion resistant design
- Suitable for building facades, sports facilities, industrial, commercial billboards, hoardings, parking lots etc.

## TECHNICAL INFORMATION

<b>Dimmable:</b>	No
<b>Model:</b>	VT-44010
<b>Instant Start:</b>	0-100% in < 1s
<b>CRI:</b>	>70
<b>Beam Angle:</b>	115°
<b>Color Temperature:</b>	4000K
<b>Watts:</b>	10
<b>Lumens:</b>	735
<b>Input Power:</b>	AC:220-240V, 50Hz
<b>Unit Color:</b>	Black
<b>Color for Web:</b>	Day White
<b>Body Type:</b>	Aluminium
<b>Dimension:</b>	104x21x92mm
<b>Operation Temperature:</b>	-20°C to +45°C
<b>LED Chip Type:</b>	SMD-Samsung Chip
<b>Energy Rating Label:</b>	F (2021)
<b>Energy Saving:</b>	85 Energy
<b>Samsung:</b>	Yes
<b>Long Life:</b>	25,000 Hours
<b>IP Rating:</b>	IP65

**IP65**  
STANDARD

**05**  
YEAR  
WARRANTY



## LISTING DETAILS

<b>SKU:</b>	9899
<b>Model:</b>	VT-44010
<b>EAN:</b>	3800170203501
<b>Commodity Code:</b>	94054210

## PACKAGING

<b>Gross Weight (Kgs):</b>	0.16
<b>Unit CBM:</b>	0.000376
<b>Dimension:</b>	104x21x92mm

## MASTER BOX PACKAGING

<b>Box Qty:</b>	40
<b>Qty Per Pallet:</b>	2880
<b>Length (Box) mm:</b>	109
<b>Width (Box) mm:</b>	26
<b>Height (Box) mm:</b>	97