



# VT-44010 10W FLOODLIGHT SAMSUNG CHIP COLORCODE:6500K WHITE BODY WHITE GLASS



## FEATURES

- Product designed with high lumen efficiency of 85 LM/W
- High quality LED SMD-Samsung Chip chip and high power driver
- Constant current Integrated IC driver - Built in driver - no external power supply required
- Built Strong and durable with Aluminium - Corrosion resistant design
- Suitable for building facades, sports facilities, industrial, commercial billboards, hoardings, parking lots etc.

## TECHNICAL INFORMATION

Dimmable:	No
Model:	VT-44010-W
Instant Start:	0-100% in <1s
CRI:	>70
Beam Angle:	115°
Color Temperature:	6500K
Watts:	10
Lumens:	735
Input Power:	AC:220-240V, 50Hz
Unit Color:	White
Color for Web:	White
Body Type:	Aluminium
Dimension:	104x21x92mm
Operation Temperature:	-20°C to +45°C
LED Chip Type:	SMD-Samsung Chip
Energy Rating Label:	F (2021)
Energy Saving:	85 Energy
Samsung:	Yes
Long Life:	25,000 Hours
IP Rating:	IP65

**IP65**  
STANDARD

**05**  
YEAR  
WARRANTY



## LISTING DETAILS

SKU:	10013
Model:	VT-44010-W
EAN:	3800170203549
Commodity Code:	94054210

## PACKAGING

Gross Weight (Kgs):	0.16
Unit CBM:	0.000375
Dimension:	104x21x92mm

## MASTER BOX PACKAGING

Box Qty:	40
Qty Per Pallet:	2880
Length (Box) mm:	109
Width (Box) mm:	26
Height (Box) mm:	97