



VT-44020 20W FLOODLIGHT SAMSUNG CHIP 3000K BLACK BODY GREY GLASS



FEATURES

- High quality LED SMD-Samsung Chip chip and high power driver
- Comparing with traditional halogen floodlights it can save upto 85% Energy
- Constant current Integrated IC driver - Built in driver - no external power supply required
- Built Strong and durable with Aluminium - Corrosion resistant design
- Suitable for building facades, sports facilities, industrial, commercial billboards, hoardings, parking lots etc.

TECHNICAL INFORMATION

Dimmable:	No
Model:	VT-44020
Instant Start:	0-100% in < 1s
CRI:	>70
Beam Angle:	115°
Color Temperature:	3000K
Watts:	20
Lumens:	1620
Input Power:	AC:220-240V, 50Hz
Unit Color:	Black
Color for Web:	Warm White
Body Type:	Aluminium
Dimension:	126.5x28x114mm
Operation Temperature:	-20°C to +45°C
LED Chip Type:	SMD-Samsung Chip
Energy Rating Label:	F (2021)
Energy Saving:	85 Energy
Samsung:	Yes
Long Life:	25,000 Hours
IP Rating:	IP65

IP65
STANDARD

05 
YEAR
WARRANTY



LISTING DETAILS

SKU:	10014
Model:	VT-44020
EAN:	3800170203556
Commodity Code:	94054210

PACKAGING

Gross Weight (Kgs):	0.25
Unit CBM:	0.0007
Dimension:	126.5x28x114mm

MASTER BOX PACKAGING

Box Qty:	20
Qty Per Pallet:	145
Length (Box) mm:	132
Width (Box) mm:	33
Height (Box) mm:	118