



VT-44153 150W FLOODLIGHT SAMSUNG CHIP 1M WIRE 4000K BLACK BODY GREY GLASS 135LM/W



FEATURES

- Product designed with high lumen efficiency of 135 LM/W
- High quality LED SMD-Samsung Chip
- Built Strong and durable with Aluminium - Corrosion resistant design
- Suitable for building facades, sports facilities, industrial, commercial billboards, hoardings, parking lots etc.

TECHNICAL INFORMATION

Dimmable:	No
Model:	VT-44153
Instant Start:	0-100% in < 1s
Beam Angle:	115°
Color Temperature:	4000K
Watts:	150
Lumens:	17220
Input Power:	AC:220-240V, 50Hz
Unit Color:	Black
Color for Web:	Day White
Body Type:	Aluminium
Dimension:	328.5x43x295mm
Operation Temperature:	-20°C to +45°C
LED Chip Type:	SMD-Samsung Chip
Energy Rating Label:	D (2021)
Energy Saving:	85 Energy
Wire Length:	1m
Samsung:	Yes
Long Life:	25,000 Hours
IP Rating:	IP65

IP65
STANDARD

05
YEAR
WARRANTY



LISTING DETAILS

SKU:	23201
Model:	VT-44153
EAN:	3800170215863
Commodity Code:	

PACKAGING

Gross Weight (Kgs):	2.05
Unit CBM:	0.00602
Dimension:	328.5x43x295mm

MASTER BOX PACKAGING

Box Qty:	4
Qty Per Pallet:	
Length (Box) mm:	331
Width (Box) mm:	48
Height (Box) mm:	298