

Product data sheet

Specifications



connection module to LXM62PD84A11000

ILM62CMD20A000

Product availability : Stock - Normally stocked in distribution facility

Main

Range of Product	PacDrive 3
Product or Component Type	Connector module
Accessory / separate part category	Connection accessories
Device short name	ILM

Complementary

[Us] rated supply voltage	250...700 V
[Uc] control circuit voltage	24 V DC - 20...25 %)
Input current	20 A
Control threshold overvoltage	860 V
Output Current	20 A
Peak output current	40 A
Physical interface	SERCOS III
Type of cooling	Natural convection
Overvoltage category	Class 3 IEC 61800-5-1
Width	1.75 in (44.5 mm)
Height	12.20 in (310 mm)
Depth	10.63 in (270 mm)
Net Weight	6.61 lb(US) (3 kg)

Environment

IP Degree of Protection	IP20
Pollution degree	2 IEC 61800-5-1

Ordering and shipping details

Category	18351-PACDRIVE3 INTEGRATED DRIVES
Discount Schedule	PC52
GTIN	3606485305523

Returnability	No
Country of origin	DE

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	14.33 in (36.4 cm)
Package 1 Width	30.94 in (78.6 cm)
Package 1 Length	11.26 in (28.6 cm)
Package 1 Weight	6.94 lb(US) (3.15 kg)
Unit Type of Package 2	P06
Number of Units in Package 2	6
Package 2 Height	30.31 in (77.0 cm)
Package 2 Width	31.50 in (80.0 cm)
Package 2 Length	23.62 in (60.0 cm)
Package 2 Weight	57.32 lb(US) (26.0 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)