



1. CRIMPED FERRULE  
HEX CRIMP SIZE .178"
2. CRIMPED CONTACT PIN  
HEX CRIMP SIZE .068"
3. MAX. PANEL THICKNESS=3.5mm

- NOTES: FINISH (PLATING THICKNESS IN MICRO-INCHES)
1. BRASS PER QQ-B-626
  2. BRASS PER QQ-B-613
  3. NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
  4. PHOSPHOR BRONZE PER QQ-B-750
  5. GOLD PL. 3 MIN. THICK OVER NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
  6. JIS H 3260, C 3501

10	FERRULE	NOTE 6	NOTE 3	1	FR-52/44-38/3X14
9	SLEEVE	DELTRIN	NATURAL	1	SL-25/17X129
8	CONTACT PIN	NOTE 4	NOTE 5	1	B74000-8-25/04
7	HEX NUT	NOTE 1	NOTE 3	1	HN16-1/2-28X28
6	LOCK WASHER	NOTE 2	NOTE 3	1	LW-16/13X05
5	GASKET	RUBBER	RED	1	GS-16/122X15
4	BARREL	NOTE 1	NOTE 3	1	B74000-4-38/27S
3	INSULATOR	DELTRIN	NATURAL	1	B74050-3-75-B
2	BODY	NOTE 1	NOTE 3	1	B74000-2
1	HOUSING	NOTE 1	NOTE 3	1	B74000-1
NO.	DESCRIPTION	MATERIAL	FINISH	Q'TY	DRAWING NO.

DIMENSIONS ARE IN MILLIMETERS			PART NO.	B6421E1-ND3G-6-75	
UNLESS OTHERWISE SPECIFIED TOLERANCES			APPROVED	DATE	10-11-01'
0.5-6 = ±0.2			CHECKED	DATE	10-11-01'
6-30 = ±0.4			DRAWN	DATE	10-11-01'
30-120 = ±0.6			FILE NO.		
120-315 = ±1					
315-1000 = ±1.6					
1000-2000 = ±2.4					

<h1>Amphenol</h1>	
TITLE BNC BULKHEAD CRIMP JACK (FOR RG-179/U,187A/U)	
DRAWING NO. KJ-B6421E1-ND3G-179U-75	
ITEM NO.	

F  
E  
D  
C  
B  
A

F  
E  
D  
C  
B  
A

1      2      3      4      5      6      7      8

1      2      3      4      5      6      7      8