

# ROLINE UTP Data Center Patch Cord Cat.6A (Class EA), LSOH, Slim, green, 1.5 m

**Product No.** 21.15.3934  
**Manufacturer** ROLINE  
**Manufacturer No.** 21.15.3934  
**EAN (single piece)** 7630049615106

**roline**  
Designed for Professionals



**Category 6A twisted-pair patch cable with RJ-45 connectors on both sides. Particularly thin and flexible cable with individual pairs of wires for use in confined spaces, such as in data centres.**

- Durable thanks to moulded-on kink protection
- Suitable as patch cable in patch panels or as device connection cable and intended for use in the LAN
- Contact assignment: 1:1 according to EIA/TIA568, 8 cores
- Structure: 8 cores stranded wire

## Technical specifications

Manufacturer	ROLINE
Product group	Twisted Pair Cable
Product type	UTP Patch Cables
Colour	green
Length	1.5 m
Shield type	UTP

Transfer quality	Cat6A / Class EA
Quantity of wires	8
Conductor type	Wire
Crossed	No
Slim cable	Yes
External cable diameter	3.4 +/- 0.2mm
Cable LSOH	Yes
Side 1 Connector Type	RJ-45
Side 1 Connector Gender	Male
Side 2 Connector Type	RJ-45
Side 2 Connector Gender	Male
Connector Type RJ45	Standard
Operating temperature min.	-10 °C
Operating temperature max.	60 °C
Weight	24.2 g
Height of packaging (single piece)	10 mm
Width of packaging (single piece)	130 mm
Depth of packaging (single piece)	140 mm
Package weight (single piece)	0.03 kg