ROLINE UTP Data Center Patch Cord Cat.6A (Class EA), LSOH, Slim, black, 0.5 m

Product No. 21.15.3952

Designed for Profession


Manufacturer

ROLINE

Manufacturer No. 21.15.3952

EAN (single piece) 7630049615243















Category 6A twisted-pair patch cable with RJ-45 connectors on both sides. Particularly thin and flexible cable with individual pairs of wires for use in confined spaces, such as in data centres.

- Durable thanks to moulded-on kink protection
- Suitable as patch cable in patch panels or as device connection cable and intended for use in the LAN
- Contact assignment: 1:1 according to EIA/TIA568, 8 cores
- Structure: 8 cores stranded wire

Technical specifications		
Manufacturer	ROLINE	
Product group	Twisted Pair Cable	
Product type	UTP Patch Cables	
Colour	black	
Length	0.5 m	
Shield type	UTP	

Transfer quality	Cat6A / Class EA
Quantity of wires	8
Conductor type	Wire
Crossed	No
Slim cable	Yes
External cable diameter	3.4 +/- 0.2mm
Cable LSOH	Yes
Side 1 Connector Type	RJ-45
Side 1 Connector Gender	Male
Side 2 Connector Type	RJ-45
Side 2 Connector Gender	Male
Connector Type RJ45	Standard
Operating temperature min.	-10 °C
Operating temperature max.	60 °C
Weight	11.3 g
Height of packaging (single piece)	10 mm
Width of packaging (single piece)	50 mm
Depth of packaging (single piece)	50 mm
Package weight (single piece)	0.01 kg