



Main

Product or component type	Industrial Control Transformer
Range of product	EO

Complementary

Phase	1 phase
Rated power in VA	500 VA
Primary voltage	230 x 460 V 220 x 440 V 240 x 480 V
Secondary voltage	110 V
Temperature rise	80 °C
Electrical connection	Screw clamp terminals

Environment

Product certifications	CE UL listed CSA
NEMA degree of protection	Not rated (open device)
Insulation temperature	266 °F (130 °C)

Ordering and shipping details

Category	21691 - 9070 AP,E,G,H,SB
Discount Schedule	CP8
GTIN	00785901723103
Returnability	Yes
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to www.p65warnings.ca.gov
RECh Regulation	RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes

China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Contractual warranty	
Warranty	18 months