



Main

Product or component type	Industrial Control Transformer
Power Rating	100 VA
Primary Voltage	208/230/460 V
Secondary Voltage	115 V
Type	TF

Complementary

Number of Phases	1 phase
Power Rating	100 VA
Primary to Secondary Voltage	208/230/460 V 115 V
Fuse type	0.41 x 1.50 in CC top
Temperature rise	55 °C
Electrical connection	Screw clamp terminals
Height	4.5 in (114.30 mm)
Width	3.75 in (95.25 mm)
Depth	3.59 in (91.19 mm)
Material	Copper winding
Fingersafe Cover Compatibility	FSC1

Environment

Product certifications	UL listed file E61239 CSA file LR37055 guide 184-N-90
Enclosure Type	Not rated (open device)
Insulation temperature	221 °F (105 °C)

Ordering and shipping details

Category	16202 - 9070 TF (NOT T) 50-200VA
Discount Schedule	CP8
GTIN	00785901905240
Returnability	Yes
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------