

9070T500D50

XFMR CONTROL 500VA

MULTIPLE VOLTAGES



Main

Product or component type	Industrial Control Transformer
Power Rating	500 VA
Primary Voltage	240/416/480/600 V 208/360/416/520 V 220/380/440/550 V 230/400/460/575 V
Secondary Voltage	90/110/120 V 85/104/115 V 95/115/125 V 99/120/130 V
Type	T

Complementary

Number of Phases	1 phase
Power Rating	500 VA UL 500 VA CSA 500 VA NOM 300 VA
Primary to Secondary Voltage	208/360/416/520 V 85/104/115 V 220/380/440/550 V 90/110/120 V 230/400/460/575 V 95/115/125 V 240/416/480/600 V 99/120/130 V
Temperature rise	115 °C
Electrical connection	Screw clamp terminals
Height	4.51 in (114.55 mm)
Width	5.25 in (133.35 mm)
Depth	5.61 in (142.49 mm)
Material	Copper winding
Fingersafe Cover Compatibility	FSC23

Environment

Product certifications	CSA file LR37055 guide 184-N-90 UL listed file E61239
Enclosure Type	Not rated (open device)
Insulation temperature	356 °F (180 °C)

Ordering and shipping details

Category	16201 - 9070 T (NOT TF) 250-2000VA
Discount Schedule	CP8
GTIN	00785901327295
Returnability	Yes
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	10 Years
----------	----------