

Main

Product or component type	Industrial Control Transformer
Power Rating	1000 VA
Primary Voltage	600 V 575 V
Secondary Voltage	115/230 V 120/240 V
Type	TF

Complementary

Number of Phases	1 phase
Power Rating	1000 VA UL 1000 VA CSA 1000 VA NOM 600 VA
Primary to Secondary Voltage	575 V 115/230 V 600 V 120/240 V
Temperature rise	115 °C
Electrical connection	Screw clamp terminals
Height	5.8 in (147.32 mm)
Width	5.25 in (133.35 mm)
Depth	6.3 in (160.02 mm)
Fingersafe Cover Compatibility	FSC2

Environment

Product certifications	CSA UL listed
Enclosure Type	Not rated (open device)
Insulation temperature	356 °F (180 °C)

Ordering and shipping details

Category	16203 - 9070 TF (NOT T) 250-1000VA
Discount Schedule	CP8
GTIN	00785901668374
Returnability	No
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------