

9070T300D50

TRFMR CONTROL 300VA

MULTIPLEVOLTAGES



Main

Product or component type	Industrial Control Transformer
Power Rating	300 VA
Primary Voltage	230/400/460/575 V 220/380/440/550 V 208/360/416/520 V 240/416/480/600 V
Secondary Voltage	85/104/115 V 95/115/125 V 90/110/120 V 99/120/130 V
Type	T

Complementary

Number of Phases	1 phase
Power Rating	300 VA UL 300 VA CSA 300 VA NOM 200 VA
Primary to Secondary Voltage	208/360/416/520 V 85/104/115 V 220/380/440/550 V 90/110/120 V 230/400/460/575 V 95/115/125 V 240/416/480/600 V 99/120/130 V
Temperature rise	80 °C
Electrical connection	Screw clamp terminals
Height	3.84 in (97.54 mm)
Width	4.5 in (114.30 mm)
Depth	5.49 in (139.45 mm)
Material	Copper winding
Fingersafe Cover Compatibility	FSC23

Environment

Product certifications	UL listed file E61239 CSA file LR37055 guide 184-N-90
Enclosure Type	Not rated (open device)
Insulation temperature	266 °F (130 °C)

Ordering and shipping details

Category	16201 - 9070 T (NOT TF) 250-2000VA
Discount Schedule	CP8
GTIN	00785901528135
Returnability	Yes
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	10 Years
----------	----------