



Main

Product or component type	Industrial Control Transformer
Power Rating	250 VA
Primary Voltage	600 V
Secondary Voltage	12/24 V
Type	T

Complementary

Number of Phases	1 phase
Power Rating	250 VA UL 250 VA CSA 250 VA NOM 160 VA
Primary to Secondary Voltage	600 V 12/24 V
Temperature rise	80 °C
Electrical connection	Screw clamp terminals
Height	3.25 in (82.55 mm)
Width	3.75 in (95.25 mm)
Depth	5.25 in (133.35 mm)
Material	Copper winding
Fingersafe Cover Compatibility	FSC2

Environment

Product certifications	UL listed file E61239 CSA file LR37055 guide 184-N-90
Enclosure Type	Not rated (open device)
Insulation temperature	266 °F (130 °C)

Ordering and shipping details

Category	16201 - 9070 T (NOT TF) 250-2000VA
Discount Schedule	CP8
GTIN	00785901689126
Returnability	No
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes

Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	10 Years
----------	----------