

### Main

|                           |                                           |
|---------------------------|-------------------------------------------|
| Product or component type | Industrial Control Transformer            |
| Power Rating              | 500 VA                                    |
| Primary Voltage           | 230 x 460 V<br>220 x 440 V<br>240 x 480 V |
| Secondary Voltage         | 110/220 V<br>120/240 V<br>115/230 V       |
| Type                      | TF                                        |

### Complementary

|                                |                                                                         |
|--------------------------------|-------------------------------------------------------------------------|
| Number of Phases               | 1 phase                                                                 |
| Power Rating                   | 500 VA UL<br>500 VA CSA<br>500 VA NOM<br>300 VA                         |
| Primary to Secondary Voltage   | 220 x 440 V 110/220 V<br>230 x 460 V 115/230 V<br>240 x 480 V 120/240 V |
| Fuse type                      | 0.41 x 1.50 in CC top                                                   |
| Temperature rise               | 115 °C                                                                  |
| Electrical connection          | Screw clamp terminals                                                   |
| Height                         | 5.13 in (130.30 mm)                                                     |
| Width                          | 4.5 in (114.30 mm)                                                      |
| Depth                          | 5.49 in (139.45 mm)                                                     |
| Material                       | Copper winding                                                          |
| Fingersafe Cover Compatibility | FSC2                                                                    |

### Environment

|                        |                                                          |
|------------------------|----------------------------------------------------------|
| Product certifications | CSA file LR37055 guide 184-N-90<br>UL listed file E61239 |
| Enclosure Type         | Not rated (open device)                                  |
| Insulation temperature | 356 °F (180 °C)                                          |

### Ordering and shipping details

|                   |                                    |
|-------------------|------------------------------------|
| Category          | 16203 - 9070 TF (NOT T) 250-1000VA |
| Discount Schedule | CP8                                |
| GTIN              | 00785901928263                     |
| Returnability     | No                                 |
| Country of origin | US                                 |

## Offer Sustainability

|                            |                                                                                                                                 |
|----------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                                                           |
| REACH Regulation           | <a href="#"> REACH Declaration</a>             |
| REACH free of SVHC         | Yes                                                                                                                             |
| EU RoHS Directive          | Compliant <a href="#"> EU RoHS Declaration</a> |
| Toxic heavy metal free     | Yes                                                                                                                             |
| Mercury free               | Yes                                                                                                                             |
| RoHS exemption information | <a href="#"> Yes</a>                           |
| China RoHS Regulation      | <a href="#"> China RoHS Declaration</a>        |
| Environmental Disclosure   | <a href="#"> Product Environmental Profile</a> |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|