



S138

1/4" 3/8" and 1/2" Square Drive Socket Set with Combination Wrenches/Screwdriver Bits







PRODUCT DETAILS

- 12-piece 1/4" hex socket set: 4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12 and 13 mm
- 10-piece 1/4" hex deep sockets 4, 5, 6, 7, 8, 9, 10, 11, 12 and 13 mm
- 1-piece 1/4" reversible ratchet, 60 teeth and two-component handle, 150 mm
- 1-piece 1/4" two-component spinner handle 150 mm
- 1-piece 1/4" sliding T-bar: 106 mm
- 1-piece 1/4" extension bar 50 mm
- 1-piece 1/4" extension bar 100 mm
- 1-piece 1/4" universal joint
- 1-piece 1/4" bit holder
- 1-piece 1/4" flexible extension bar 150 mm/6"
- 16-piece 3/8" hex sockets 6, 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 21 and 22 mm
- 1-piece 3/8" reversible ratchet, 60 teeth and two-component handle, 200 mm
- 1-piece 3/8" spark plug socket: 21 mm/13/16"
- 1-piece 3/8" spark plug socket: 18 mm
- 1-piece 3/8" spark plug socket 16 mm/5/8"
- 1-piece 3/8" universal joint
- 1-piece 3/8" extension bar 75 mm
- 1-piece 3/8" extension bar 150 mm
- 18-piece 1/2" hex sockets 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 21, 22, 23, 24, 27, 32 and 34 mm
- 9-piece 1/2" hex sockets, 3/8", 7/16", 1/2", 9/16", 11/16", 3/4", 13/16", 7/8", 1-3/16"
- 1-piece 1/2" reversible ratchet: 60 teeth and two-component handle, 250 mm
- 1-piece 1/2" sliding T-bar with double function, 1/2" head 3/8F-1/2" M adaptor
- 1-piece 1/2" extension bar: 125 mm
- 1-piece 1/2" extension bar: 250 mm
- 1-piece 1/2" universal joint
- 1-piece bits adaptor 1/4" square drive
- 4-piece Pozidriv bits, PZ0, PZ1, PZ2 and PZ3
- 5-piece Phillips bits: PH0, PH1, PH2, PH3 and PH4
- 3-piece flat bits, 4, 5.5 and 7 mm
- 6-piece insert bits, 3, 4, 5, 6, 8 and 10 mm
- 9-piece TORX® bits, T8, T10, T15, T20, T25, T27, T30, T40 and T45
- 1-piece bits ratchet
- 3-piece hexagon L-keys, 1.5, 2 and 2.5 mm
- 8-piece 3/8" square crow foot wrench, 10, 11, 13, 14, 15, 17, 18 and 19 mm
- 13-piece combination spanners: 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18 and 19 mm
- Matte finish
- High-performance alloy steel
- Less wear and damage to fastener thanks to Dynamic-Drive™ profile sockets
- Easier access with the thin compact head on combi wrench
- Comfortable grip of spanners from the U-shaped handle
- Quick socket release button on ratchet
- Case: high density polythene (HDPE)
- Standards: ISO 1174 and DIN 3120

Follow the Fish!



PRODUCT ATTRIBUTES

| Product |  |  |  |  |
|---------|---|---|---|---|
| S138 | 430 mm | 375 mm | 110 mm | 10580 g |

