



**Double open-end spanner Metric, 6M/**

Set of Double open-end spanners in Metric sizes.  
DIN 3110 / ISO 1085 / ISO 10102

**Finish:** nickel and chrome-plated, fine-polished.

**Material:** VANADIUM-EXTRA.

Angle 15°. Model with extremely flat heads.

In plastic clip.

**6M/S8** in attractive sales cardboard box.



6M/8T	1832476	1	8	6x7 8x9 10x11 12x13 14x15 16x17 18x19 20x22	735	
6M/10T	1832490	1	10	6x7 8x9 10x11 12x13 14x15 16x17 18x19 20x22 24x27 30x32	1570	
6M/12T	1832506	1	12	6x7 8x9 10x11 12x13 14x15 16x17 18x19 20x22 21x23 24x27 25x28 30x32	2070	
6M/S8	1832483	1	8	6x7 8x9 10x11 12x13 14x15 16x17 18x19 20x22	735	
6M-DIN/ISO/8T	1838096	1	8	6x7 8x9 10x11 12x13 14x15 16x17 18x21 19x22	735	