



VT-8030 PIR CEILING SENSOR WITH MOVING HEAD (MAX:400W LED)



FEATURES

- Infrared motion sensor with integrated circuit can detect heat signatures
- Adjustable Time Delay - Ambient light - Detection distance for versatile scenarios
- High quality receptors for instant functioning
- Effective system for energy saving and safety
- Compatible with V-TAC models

TECHNICAL INFORMATION

Model:	VT-8030
Detection Range:	360°
Time Delay:	Min 10sec±3sec, Max 15min±2min
Rated Load:	Max 400W LED
Detection Motion Speed:	0.6-1.5m/s
Ambient Light:	<3-2000LUX(adjustable)
Installation Type:	Recessed
Detection Angle:	360
Detection Distance:	Max 8m(<24°C)
Input Power:	AC:220-240V, 50/60Hz
Unit Color:	White
Body Type:	PC
Dimension:	98x73x82mm
Sensor Type:	Infrared
IP Rating:	IP20

EMC Certificate: [Check the certificate](#)

LVD Certificate: [Check the certificate](#)

ROHS Certificate: [Check the certificate](#)

IP20
STANDARD

LISTING DETAILS

SKU:	5091
Model:	VT-8030
EAN:	3800157609227
Commodity Code:	85365080

PACKAGING

Gross Weight (Kgs):	0.13
Unit CBM:	0.00068
Dimension:	98x73x82mm

MASTER BOX PACKAGING

Box Qty:	50
Qty Per Pallet:	2000
Length (Box) mm:	98
Width (Box) mm:	73
Height (Box) mm:	82