



# VT-08 8W FULL ROUND DOME LIGHT 2D BULKHEAD SAMSUNG CHIP 4000K



## FEATURES

- Fitted with high efficiency Samsung LED Chips
- Efficient thermal management technology
- 100% PC for endurance & durability
- Quick connector for easy wiring
- IP65 ingress protection perfect for outdoor use
- Suitable for open areas constantly exposed to dust and moisture like parking\_x000D\_lots, corridors, airports, and malls

## TECHNICAL INFORMATION

|                      |                      |
|----------------------|----------------------|
| Dimmable:            | No                   |
| Model:               | VT-08-N              |
| Instant Start:       | 0-100% in <1s        |
| CRI:                 | >80                  |
| Beam Angle:          | 110°                 |
| Color Temperature:   | 4000K                |
| Watts:               | 8                    |
| Lumens:              | 750                  |
| Input Power:         | AC:200-240V, 50/60Hz |
| Unit Color:          | White                |
| Color for Web:       | Day White            |
| Body Type:           | PC                   |
| Dimension:           | 270x90mm             |
| Shape:               | Round                |
| PF:                  | >0.7                 |
| LED Chip Type:       | SMD-Samsung Chip     |
| Energy Rating Label: | F (2021)             |
| IK Rating:           | IK08                 |
| Samsung:             | Yes                  |
| Long Life:           | 30,000 Hours         |
| IP Rating:           | IP65                 |

**IP65**  
STANDARD

**05**  
YEAR  
WARRANTY



## LISTING DETAILS

|                 |               |
|-----------------|---------------|
| SKU:            | 21815         |
| Model:          | VT-08-N       |
| EAN:            | 3800157676717 |
| Commodity Code: | 94051140      |

## PACKAGING

|                     |          |
|---------------------|----------|
| Gross Weight (Kgs): | 0.67     |
| Unit CBM:           | 0.009047 |
| Dimension:          | 270x90mm |

## MASTER BOX PACKAGING

|                  |     |
|------------------|-----|
| Box Qty:         | 10  |
| Qty Per Pallet:  |     |
| Length (Box) mm: | 280 |
| Width (Box) mm:  | 100 |
| Height (Box) mm: | 280 |