COLORband T3BT ILS

- Full-size linear wash light with built-in Bluetooth® wireless technology
- · ILS compatibility for use in the ILS ecosystem
- D-Fi USB compatibility for wireless master/slave or DMX control
- Control directly from a smart phone or tablet without any additional hardware
- · 3 zones of control create amazing, automated effects
- Easily set static colors or automated programs with the optional IRC-6 remote
- Save time running cables and extension cords by power linking multiple units
- Fits best in the CHS-60 VIP Gear Bag



Specifications

DMX Channels: 3, 5 or 13DMX Connectors: 3-pin XLR

 Light Source: 12 LEDs (tri-color RGB), 3 W (1 A) 50,000 hours life expectancy

Strobe Rate: 0 to 25 Hz

Beam Angle: 53°
Field Angle: 83°
Coverage Angle: 112°

• Illuminance: 433 lux @ 2 m

Power Linking: 13 units @ 120 V; 24 units @ 230 V

Input Voltage: 100 to 240 VAC, 50/60 Hz (auto-ranging)

Power and Current: 43 W, 0.6 A @ 120 V, 60 Hz

Power and Current: 41 W, 0.3 A @ 230 V, 50 Hz

• Weight: 6.6 lb (3 kg)

Optional Controllers: IRC-6

• Approvals: CE, RoHS, UKCA, FCC

• Bluetooth version: 4.2

Max Unobstructed Distance: 150 ft (45.7 m)

· Operating Frequency: 2.4GHz

Size: 39.3 x 3.8 x 5.5 in (1000 x 98 x 140 mm)



