


SMAF-MMCXM316XX

(Cable Assembly Coaxial SMA Female to MMCX Male RG-316)





Toll Free: 800.955.2629

Phone: 330.780.2525

Fax: 330.780.2524

Electrical Ratings

Electrical ratings of a cable assembly are determined by the limiting connector type and cable size.

Connector	Cable	Connector	Frequency	VSWR
		Impedance	(GHz)	
		(Ohms)		
SMA	RG-316	50	0-3	1.35
				MAX
MMCX	RG-316	50	0-3	1.35
				MAX

Product Attributes

110ddet/tetilbates		
Gender	Male to Male	
Style	SMA to MMCX	
1st Connector	Gold Plated SMA Female w/ PTFE	
	Insulator	
2nd Connector	Gold Plated MMCX Connector w/	
	PTFE Insulator	
Features	Shielded	
Operating Temperature	-65°C (-85°F) to 145°C (293°F)	
SMAF-MMCXM31605	0.5M	
RoHS 3 Compliant		

Toll Free: 800.955.2629

Phone: 330.780.2525

Fax: 330.780.2524