



This item includes:

 Item No.: 2773-402 COMPACT splicing connector; for solid and stranded conductors; max. 4 mm²; 2-conductor; transparent housing; white cover; Surrounding air temperature: max 85°C (T85); 4,00 mm²; transparent	 Item No.: 2773-408 COMPACT splicing connector; for solid and stranded conductors; max. 4 mm²; 8-conductor; transparent housing; light gray cover; Surrounding air temperature: max 85°C (T85); 4,00 mm²; transparent	 Item No.: 2773-403 COMPACT splicing connector; for solid and stranded conductors; max. 4 mm²; 3-conductor; transparent housing; orange cover; Surrounding air temperature: max 85°C (T85); 4,00 mm²; transparent	 Item No.: 2773-404 COMPACT splicing connector; for solid and stranded conductors; max. 4 mm²; 4-conductor; transparent housing; red cover; Surrounding air temperature: max 85°C (T85); 4,00 mm²; transparent	60
 Item No.: 2773-405 COMPACT splicing connector; for solid and stranded conductors; max. 4 mm²; 5-conductor; transparent housing; yellow cover; Surrounding air temperature: max 85°C (T85); 4,00 mm²; transparent	 Item No.: 2773-406 COMPACT splicing connector; for solid and stranded conductors; max. 4 mm²; 6-conductor; transparent housing; Gray cover; Surrounding air temperature: max 85°C (T85); 4,00 mm²; transparent			40

Physical data

Width	260 mm / 10.236 inches
Height	63 mm / 2.48 inches
Depth	155 mm / 6.102 inches

Material data

Note (material data)	Information on material specifications can be found here
Fire load	5.49 MJ
Weight	1006.4 g



Commercial data		
ETIM 8.0		EC000446
ETIM 7.0		EC000446
PU (SPU)		1 pcs
Packaging type		Box
Country of origin		DE
GTIN		4055143951319
Customs tariff number		85369010000

Environmental Product Compliance	
RoHS Compliance Status	Compliant,No Exemption

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 887-954

↓