

Digital Terrestrial Meter



- Signal strength and BER displayed together.
- C/N and post BER displayed sub menu.
- 10 pre-programmed transmitters (via website) or all channel step through
- Audible tune-in, with back light
- 7 or 8 MHz channels
- 2K and 8K mode
- VHF (band3) and UHF bands
- External power for mast amplifiers, etc.
- Run time with full charge: Minimum 5 hours from 2.5 Ah battery
- Figure of 8 mains input connector. 2.1 mm Female PSU plug for external charge via supplied car charger.
- Computer interface: Serial port (Com 1-4) for upgradeable software on transmitters.

Technical Specification

- * Universal charger 90 V ~ 250 V Ac for above
- * 2.1 mm Female PSU plug for external charge
- * Built in NiMH battery 2.4 Ah 7.2 V
- * Figure of 8 mains input connector
- * Automatic Transmission and constellation
- * RF input range 167-862 MHz
- * Input dynamic range -72dBm~20dBm
- * Input connector BNC. Input imp75 ohms. Loop through
- * Built in universal charger 80-250 V Ac. Intelligent charger (CE approved) with delta detection. Fast charge, then Trickle.