



VT-2386 6W G45 LED FILAMENT BULB-CLEAR GLASS 4000K E27(130LM/WATT)



FEATURES

- Modern Clear filament Filament technology for better reliability and durability
- Replaces 60 watts old halogen lamp
- Lasts hours, longer life span than Standard halogen lamps.
- Designed for E27 standard holder
- High color rendering index CRI >80
- Suitable for residential lighting, commercial lighting, decorative, living rooms, lounges etc.

TECHNICAL INFORMATION

Dimmable:	No
CRI:	>80
Body Type:	Glass
Color Temperature:	4000K
Model:	VT-2386
Watts:	6
Lumens:	800
Input Power:	AC:200-240V, 50Hz
Equivalence Watts:	60
Unit Color:	Transparent
Color for Web:	Day White
Dimension:	45x72mm
Operation Temperature:	-20°C to +45°C
On/Off Cycles:	>15000
Base:	E27
Shape:	G45
Beam Angle:	300°
PF:	>0.5
LED Chip Type:	Filament
Long Life:	20,000 Hours
IP Rating:	IP20
Energy Rating Label:	E (2021)
Energy Saving:	85 Energy



IP20
STANDARD

02
YEAR
WARRANTY

Super Bright
130
LUMENS/W

LISTING DETAILS

SKU:	2852
Model:	VT-2386
EAN:	3800157659307
Commodity Code:	85395200

PACKAGING

Gross Weight (Kgs):	0.03
Unit CBM:	0.0002
Dimension:	45x72mm

MASTER BOX PACKAGING

Box Qty:	100
Qty Per Pallet:	5400
Length (Box) mm:	45
Width (Box) mm:	45
Height (Box) mm:	75