



VT-2327 6W CANDLE FILAMENT BULB CLEAR COVER 4000K E14 133LM/W



FEATURES

- Modern Clear filament Filament technology for better reliability and durability
- Replaces 55 watts old halogen lamp
- Lasts hours, longer life span than Standard halogen lamps.
- Designed for E14 standard holder
- High color rendering index CRI >80
- Suitable for residential lighting, commercial lighting, decorative, living rooms, lounges etc.

TECHNICAL INFORMATION

CRI:	>80
Body Type:	Glass
Color Temperature:	4000K
Model:	VT-2327-N
Watts:	6
Lumens:	800
Input Power:	AC:220-240V, 50Hz
Equivalence Watts:	55
Unit Color:	Transparent
Color for Web:	Day White
Dimension:	35x98mm
Operation Temperature:	-20°C to +45°C
Instant Start:	0-100% in < 1s
On/Off Cycles:	>15000
Base:	E14
Shape:	Candle
Beam Angle:	300°
LED Chip Type:	Filament
Long Life:	20,000 Hours
IP Rating:	IP20
Energy Rating Label:	E (2021)
Energy Saving:	80 Energy



IP20
STANDARD

02
YEAR
WARRANTY

LISTING DETAILS

SKU:	212849
Model:	VT-2327-N
EAN:	3800157691949
Commodity Code:	

PACKAGING

Gross Weight (Kgs):	0.02
Unit CBM:	0.000158
Dimension:	35x98mm

MASTER BOX PACKAGING

Box Qty:	100
Qty Per Pallet:	
Length (Box) mm:	35
Width (Box) mm:	35
Height (Box) mm:	100