



VT-1821 4.5W LED CANDLE BULB 4000K E27



FEATURES

- Modern LED SMD technology for better reliability and durability
- Replaces 40 watts old halogen lamp
- Lasts hours, longer life span than Standard halogen lamps
- Designed for E27 standard holder
- Suitable for residential lighting, commercial lighting, decorative, living rooms, lounges etc.

TECHNICAL INFORMATION

CRI:	>80
Body Type:	Thermoplastic
Color Temperature:	4000K
Model:	VT-1821-N
Watts:	4.5
Lumens:	470
Input Power:	AC:220-240V,50Hz
Equivalence Watts:	40
Unit Color:	White
Color for Web:	Day White
Dimension:	36.5x100mm
On/Off Cycles:	>20000
Base:	E27
Shape:	Candle
Beam Angle:	180°
LED Chip Type:	SMD
Long Life:	20,000 Hours
IP Rating:	IP20
Energy Rating Label:	F (2021)



IP20
STANDARD

02
YEAR
WARRANTY

LISTING DETAILS

SKU:	2143431
Model:	VT-1821-N
EAN:	3800157682596
Commodity Code:	85395200

PACKAGING

Gross Weight (Kgs):	0.03
Unit CBM:	0.000198
Dimension:	36.5x100mm

MASTER BOX PACKAGING

Box Qty:	200
Qty Per Pallet:	7000
Length (Box) mm:	35
Width (Box) mm:	35
Height (Box) mm:	105