



## VT-1821 4.5W LED CANDLE BULB 6500K E27



### FEATURES

- Modern LED SMD technology for better reliability and durability
- Replaces 40 watts old halogen lamp
- Lasts hours, longer life span than Standard halogen lamps
- Designed for E27 standard holder
- Suitable for residential lighting, commercial lighting, decorative, living rooms, lounges etc.

### TECHNICAL INFORMATION

|                      |                   |
|----------------------|-------------------|
| Dimmable:            | No                |
| CRI:                 | >80               |
| Body Type:           | Thermoplastic     |
| Color Temperature:   | 6500K             |
| Model:               | VT-1821N-N        |
| Watts:               | 4.5               |
| Lumens:              | 470               |
| Input Power:         | AC:220-240V, 50Hz |
| Equivalence Watts:   | 40                |
| Unit Color:          | White             |
| Color for Web:       | White             |
| Dimension:           | 36.5x100mm        |
| On/Off Cycles:       | >20000            |
| Base:                | E27               |
| Shape:               | Candle            |
| Beam Angle:          | 180°              |
| PF:                  | >0.5              |
| LED Chip Type:       | SMD               |
| Long Life:           | 20,000 Hours      |
| IP Rating:           | IP20              |
| Energy Rating Label: | F (2021)          |



IP20  
STANDARD

02  
YEAR  
WARRANTY

### LISTING DETAILS

|                 |               |
|-----------------|---------------|
| SKU:            | 2143441       |
| Model:          | VT-1821N-N    |
| EAN:            | 3800157676427 |
| Commodity Code: | 85395200      |

### PACKAGING

|                     |            |
|---------------------|------------|
| Gross Weight (Kgs): | 0.03       |
| Unit CBM:           | 0.000195   |
| Dimension:          | 36.5x100mm |

### MASTER BOX PACKAGING

|                  |      |
|------------------|------|
| Box Qty:         | 10   |
| Qty Per Pallet:  | 7000 |
| Length (Box) mm: | 35   |
| Width (Box) mm:  | 35   |
| Height (Box) mm: | 105  |